



Torque screwdriver with scale, maximum torque: 15cNm



Order data

Order number	659939 15
GTIN	4560138455906
Item class	66F

Description

Version:

Torque screwdrivers with over-torque protection for different applications from series production to maintenance work. With a locking mechanism that prevents adjustment of the torque when in use. The hexagon lock shape prevents rolling away. Setting by using micrometer scale. Profiled light metal handle.

Function:

When the set torque is reached the screwdriver triggers and signals clearly (audibly and perceptibly). It is then again immediately ready for use. The trigger mechanism is unavailable for tightening left-handed threads.

Standard:

Geprüft nach DIN EN ISO 6789.

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

Ø	16 mm
Scale graduation, 1 graduation =	0.1 cNm
Torque measuring accuracy	±3 %
maximum torque	15 cNm
Display	analogue
Bit socket	F 6.3

Torque range	2 - 15 cNm
Torque range	0.02 - 0.15 Nm
Reversible reading	Nm
Weight	50 g
Adjustable trigger value	adjustable
Connection format	Bit holder 1/4 inch
Overall length L	100 mm
Feedback	triggering
Measurement process	Torque
Trigger principle	mechanical slip clutch
Setting the trigger value	with adjustment scale
Standard	DIN EN ISO 6789
Calibration	O1
Direction of tightening	Right-hand tightening
Test certificate	Manufacturer's test certificate
Data can be recorded	no
Measurement technology	mechanical
Release signalling	optisk
Release signalling	akustisk
Type of product	Torque screwdriver

Services

CalibrationTorque screwdriver maximum torque 0,04-20 N·m	020200 0,04-20
--	----------------