

**Garant****Solid carbide HPC drill plain shank DIN 6535 HA, TiAlN, Ø DC h7: 16,01-Xmm****Order data**

Order number	122690 16,01-X
GTIN	4062406200947
Item class	11E

**Description****Version:**

**3 guide chamfers** for particularly high accuracy and surface quality at tight hole tolerances.

**Asymmetrical tip geometry** for **very high metal removal rates**. New generation of **innovative high-performance drills for cast iron** in the HPC field.

**Advantage:**

For HPC high performance drilling in castings. **Outstandingly suitable for bainite cast iron (ADI).**

**Note:**

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

Form HB and HE supplied at the same price as HA.

Form **HB**: order with **No. 122690 + 129100HB**.

Form **HE**: order with **No. 122690 + 129100HE**. Delivery time: 8 weeks

Minimum order quantity: 3 pcs.

Items made to order for a specific customer: Cancellation only up to a maximum of 3 working days after receipt of order acknowledgement. Items cannot be returned. We reserve the right to over or under deliver by +/-10% (min. 1 pc).

**Technical description**

Flute length $L_c$	93 mm
Standard	DIN 6537
Shank Ø $D_s$	18 mm
Number of cutting edges Z	2
Ø range	16.01 - 18 mm
Tolerance nominal Ø	h7

Overall length L	143 mm
Coating	TiAlN
Tool material	Solid carbide
Version	6×D
Point angle	135 degrees
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	white
Type of product	Jobber drill

## User data

	Suitability	V <sub>c</sub>	ISO code
GG	suitable	110 m/min	K
GGG	suitable	90 m/min	K
GJS, ADI > 800N/mm <sup>2</sup>	suitable	70 m/min	K
wet maximum	suitable		
wet minimum	suitable		