



FlyMarker® mini 65/30 needle marker Cordless, Battery capacity:Ah

Order data

Order number	085757
GTIN	2050001940254
Item class	04F

Description

Version:

For permanent identification / marking / lettering of batch and series production parts of different materials (steel, stainless steel, aluminium, copper, brass, plastics, tool steel, hardened steels up to 62 HRC, etc.).

- **Powerful electro-magnetic marking needle drive.**
- **Simple intuitive software with password protection.**
- **High-resolution colour display.**
- **Marking preview for reliable marking.**
- **Unbreakable housing.**
- **Interfaces: USB-A, USB-B and Ethernet.**
- **Font: Dot matrix in a 5×7 or 9×13 grid, font height 1.0 – 10.0 mm and larger.**
- **Fonts for character heights greater than 10.0 mm on request.**
- **High-quality double linear guides for precise marking results.**
- **Round parts can be marked radially and axially, and also in an arc of a circle.**
- **Supplied with an HPGL pack (for marking individual logos and inspection symbols, CE marks etc.)**
- **Supplied with a convenience pack (e.g. for shift identification, pre-positioning, multiple marking, etc.)**
- **Internal memory for several hundred marking files, fonts and logos.**
- **Available in 15 languages.**

Standard:

For permanent identification / marking / lettering of batch and series production parts of different materials (steel, stainless steel, aluminium, copper, brass, plastics, tool steel, hardened steels up to 62 HRC, etc.).

- **Powerful electro-magnetic marking needle drive.**
- **Simple intuitive software with password protection.**
- **High-resolution colour display.**
- **Marking preview for reliable marking.**

Supplied with:

Tool kit, solid carbide marking needle 90° adjustment bracket with non-slip coating, setting gauge, and carrying case, **2x18 V Li-ion rechargeable batteries**, charger.

maximum marker field width: 65 mm

maximum marker field height: 30 mm

Technical description

maximum marker field height	30 mm
maximum marker field width	65 mm
Type of product	