



Hinged pin wrench offset, largest \varnothing / pin nominal \varnothing : 40/4mm



Order data

Order number	628810 40/4
GTIN	4020772051068
Item class	63Q

Description

Version:

Special steel, drive head ground, annealed and burnished.
Cranked, with interchangeable pins.

Application:

For twin hole nuts.

Note:

Pin \varnothing = pin nominal \varnothing - 0.1 mm; tolerance field h12.

Technical description

Pin spacing adjustable a	18 - 40 mm
largest \varnothing	40 mm
overall length	158 mm
Pin nominal \varnothing	4 mm
Type	764C
Pin thread	M4
Manufacturer's designation	764CC
Type of product	Pin spanner

