

**Circular saw blade expert for Steel, Blade Ø D: 210mm****Order data**

Order number	583910 210
GTIN	3165140737708
Item class	54B

Description**Version:**

Precision saw blade with high-strength, **noise and vibration suppressing blade body**. The tensioning ring incorporated ensure stability of the shape in all temperature ranges. The **coating** prevents adhesions, keeps the saw blade cool and protects it against corrosion. **Precision-ground carbide teeth** ensure a long working life and best quality of cut.

Application:

For **machining steel**. Special anchoring of the carbide teeth in the base blade prevents teeth breaking off. Tooth form: Trapezoidal flat teeth (with chamfer), neutral rake angle. For hand-held dry-cutting hacksaws.

Note:

Further circular saw blades can be found in Group 17.

Technical description

Ø	210 mm
Bore Ø	30 mm
Number of teeth	48

Width of cut B	2 mm
Type of product	Circular saw blade