


**Velour-backed abrasive disc (A) 15 holes, Ø 150 mm, Grit: 220****Order data**

|              |               |
|--------------|---------------|
| Order number | GG5779 220    |
| GTIN         | 4062406201845 |
| Item class   | GGN           |

**Description****Version:**

Dust-repellent coating prevents premature clogging. The back is covered with hook and loop backing.

Velour-backed abrasive disc with semi-open distribution, aluminium oxide (A).

Corresponds to 567790.

**Application:**

On **orbital sanders** with hook and loop pads e.g.No. 567990 (dust extraction available).

Universal **all-round product** for coarse, intermediate and fine abrasion on all metal and plastic surfaces, paint systems and woods.

Universal **all-round product** for coarse, intermediate and fine abrasion on all metal and plastic surfaces, paint systems and woods.

**Technical description**

|          |        |
|----------|--------|
| Disc Ø   | 150 mm |
| Grit     | 220    |
| Contents | 500    |

|   |                             |
|---|-----------------------------|
| Grinding medium code                    | A                           |
| Iron, sulphur and chlorine constituents | < 0.1 %                     |
| Product name attribute                  | Ø 150 mm                    |
| Number of dust extraction holes         | 15                          |
| Propulsive equipment                    | Orbital sander              |
| maximum circumferential speed           | 40 m/s                      |
| Type of product                         | Velour-backed abrasive disc |

## User data

|                                | Suitability                               | V <sub>c</sub> | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg                         | suitable                                  |                |          |
| Steel < 900 N/mm <sup>2</sup>  | suitable                                  |                |          |
| Steel < 1400 N/mm <sup>2</sup> | suitable                                  |                |          |
| Steel < 55 HRC                 | suitable                                  |                |          |
| Steel < 60 HRC                 | suitable                                  |                |          |
| Steel < 67 HRC                 | suitable only under restricted conditions |                |          |
| INOX                           | suitable                                  |                |          |
| Ti                             | suitable only under restricted conditions |                |          |
| CuZn                           | suitable                                  |                |          |
| Plastic, GRP                   | suitable                                  |                |          |
| Wood                           | suitable                                  |                |          |
| Paint                          | suitable                                  |                |          |
| Uni                            | suitable                                  |                |          |
| dry                            | suitable                                  |                |          |

## Accessories

|   |            |
|---|------------|
| Multi-hole PU backing pad External Ø 147 mm | 567990 147 |
|---|------------|

|  |            |
|--|------------|
| PU hook and loop backing pad External Ø 150 mm             | 567885 150 |
| PU hook and loop backing pad Multiple holes Outer Ø 150 mm | 567887 150 |
| Velour-backed abrasive disc (A) 15 holes Grit 220          | 567790 220 |