



Solid carbide slot drill, uncoated, Ø e8 DC: 1mm

Order data

Order number	GG2307 1
GTIN	4062406199104
Item class	GGN

Description
Version:

 Dimensions similar to **DIN 6527**.

Same as No. 202307.
Technical description

Flute length L_c	3 mm
Feed f_z for side milling in steel $< 750 \text{ N/mm}^2$	0.006 mm
Tolerance nominal \varnothing	e8
Overall length L	50 mm
No. of teeth Z	3
Feed f_z for slot milling in steel $< 750 \text{ N/mm}^2$	0.005 mm
Cutting edge $\varnothing D_c$	1 mm
Shank $\varnothing D_s$	3 mm
Shank	DIN 6535 HA to h6
Direction of infeed	horizontal, oblique and vertical

Shank form	HA
Helix angle	45 degrees
Corner chamfer angle	90 degrees
Contents	5
Coating	uncoated
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Through-coolant	no
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Alu plastics	suitable only under restricted conditions	170 m/min	N
Aluminium (short chipping)	suitable	140 m/min	N
Alu > 10% Si	suitable	100 m/min	N
Steel < 500 N/mm ²	suitable	70 m/min	P
Steel < 750 N/mm ²	suitable	60 m/min	P
Steel < 900 N/mm ²	suitable	45 m/min	P
INOX < 900 N/mm ²	suitable only under restricted conditions	40 m/min	M
GG(G)	suitable only under restricted conditions	55 m/min	K
Uni	suitable only under restricted conditions		
wet maximum	suitable		

wet minimum	Suitable
dry	suitable only under restricted conditions
Air	Suitable

Accessories

Solid carbide milling cutter Ø e8 DC 1 mm	202307 1
---	----------