

Garant

Solid carbide HPC drill plain shank DIN 6535 HA, TiAlN, Ø DC h7: 8,01-Xmm



Order data

Order number	122690 8,01-X
GTIN	4062406200909
Item class	11E

Description

Version:

3 guide chamfers for particularly high accuracy and surface quality at tight hole tolerances.
Asymmetrical tip geometry for **very high metal removal rates**. New generation of **innovative high-performance drills for cast iron** in the HPC field.

Advantage:

For HPC high performance drilling in castings. **Outstandingly suitable for bainite cast iron (ADI)**.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Form HB and HE supplied at the same price as HA.

Form **HB**: order with **No. 122690 + 129100HB** .

Form **HE**: order with **No. 122690 + 129100HE**. Delivery time: 8 weeks

Minimum order quantity: 3 pcs.

Items made to order for a specific customer: Cancellation only up to a maximum of 3 working days after receipt of order acknowledgement. Items cannot be returned. We reserve the right to over or under deliver by +/-10% (min. 1 pc).

Technical description

Overall length L	103 mm
Number of cutting edges Z	2
Tolerance nominal Ø	h7
Ø range	8.01 - 10 mm
Standard	DIN 6537
Flute length L_c	61 mm

Shank $\varnothing D_s$	10 mm
Coating	TiAlN
Tool material	Solid carbide
Version	6xD
Point angle	135 degrees
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	white
Type of product	Jobber drill

User data

	Suitability	V_c	ISO code
GG	suitable	110 m/min	K
GGG	suitable	90 m/min	K
GJS, ADI > 800N/mm ²	suitable	70 m/min	K
wet maximum	suitable		
wet minimum	suitable		