

Garant

GARANT Master Steel FEED solid carbide drill, Weldon shank DIN 6535 HB, TiAlN, Ø DC h7: 18,01-Xmm



Order data

| | |
|--------------|----------------|
| Order number | 123236 18,01-X |
| GTIN | 4062406201524 |
| Item class | 11E |

Description

Version:

3-flute drill, specially developed for **use at very high feed rates**. Outstandingly suitable for machines with **high installed power** and stable machining conditions.

- **Special cutter geometry with stable cutting edges and large clearance at the centre enables very high feed rates.**
- **The patented tip is optimised for chip flow and generates low cutting pressure with good chip breakage.**

The **sector-leading technology of the drill point** guarantees **optimum self-centring behaviour**. 3 guide chamfers guarantee a stable exit from the hole and an exact roundness of the hole.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

For process reliability when using the 12xD deep-hole drill, an initial centre drilling with an NC spotting drill No. 121130 with **155° point angle** is necessary. Delivery time: 8 weeks

Minimum order quantity: 3 pcs.

Items made to order for a specific customer: Cancellation only up to a maximum of 3 working days after receipt of order acknowledgement. Items cannot be returned. We reserve the right to over-deliver or under-deliver by +/-10% (minimum 1 piece).

Technical description

| Standard | Manufacturer's standard |
|--------------------|-------------------------|
| Overall length L | 310 mm |
| Flute length L_c | 258 mm |
| Shank Ø D_s | 20 mm |

| | |
|---------------------------|-------------------|
| Ø range | 18.01 - 20 mm |
| Number of cutting edges Z | 3 |
| Tolerance nominal Ø | h7 |
| Series | Master Steel |
| Coating | TiAlN |
| Tool material | Solid carbide |
| Version | 12xD |
| Point angle | 140 degrees |
| Shank | DIN 6535 HB to h6 |
| Through-coolant | yes, to 25 bar |
| Machining strategy | HPC |
| Semi-Standard | yes |
| Colour ring | green |
| Type of product | Jobber drill |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Steel < 500 N/mm ² | suitable | 120 m/min | P |
| Steel < 750 N/mm ² | suitable | 110 m/min | P |
| Steel < 900 N/mm ² | suitable | 100 m/min | P |
| Steel < 1100 N/mm ² | suitable | 90 m/min | P |
| Steel < 1400 N/mm ² | suitable | 70 m/min | P |
| Steel < 55 HRC | suitable | 60 m/min | H |
| INOX < 900 N/mm ² | suitable | 55 m/min | M |
| INOX > 900 N/mm ² | suitable | 50 m/min | M |
| Ti > 850 N/mm ² | suitable only under restricted conditions | 40 m/min | S |
| GG | suitable | 120 m/min | K |
| GGG | suitable | 80 m/min | K |

| | |
|-------------|----------|
| Uni | suitable |
| wet maximum | suitable |
| wet minimum | suitable |