



Abrasive flap disc long life ZA, conical, Ø 125 mm, Grit: 60



Order data

Order number	GG5285 60
GTIN	4062406201647
Item class	GGN

Description

Version:

- **High-quality zirconium aluminium oxide (ZA) for high abrasive performance.**
- **Glass fibre pad for optimum contact pressure.**
- **Suitable for both steel and stainless steel.**
- **Best results on angle grinders of all power classes.**

long life - very closely spaced flap strips, for **maximum tool life**.

Corresponds to 565285.

Application:

General purpose abrasive disc operations, surface abrasion, material removal and edge smoothing.

Supplied with:

100 pcs. abrasive flap disc No. 565285.

Note:

Only sold in bulk pack quantities, not supplied individually. Ordering information: 1 set = 1 bulk pack.

Technical description

Disc Ø	125 mm
--------	--------

Grit	60
Bore Ø	22.23 mm
Shape description	dished
Contents	100
Grinding media	Zirconium abrasive (ZA)
Grinding medium code	ZA
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 125 mm
optimised for material	INOX
optimised for material	Steel
maximum circumferential speed	80 m/s
Type of product	Abrasive flap disc

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
Uni	suitable		
dry	suitable		

Accessories

Abrasive flap disclong life ZA, conical Grit 60

565285 60