

**BENNING****Voltage tester DUSPOL<sup>®</sup>, Device type: PROFIPOL+****Order data**

Order number	473105 PROFIPOL+
GTIN	4014651200234
Item class	47A

**Description****Version:**

With test handle stop for one-handed operation at socket outlets and for secure storage. The voltage display is operational even if the batteries are flat or have been taken out.

**Function:**

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

**Application:**

Suitable for manual crafts, and for working on electrical systems, industrial systems, maintenance, servicing (troubleshooting),

**Standard:**

**DIN EN 61243-3, VDE 0682-401:2015**

**Technical description**

Polarity testing	LED
Continuity testing	acoustic / LED
Display	LED
Display range AC	12 - 690 V

Phase testing	LED
contactless detection of broken cables	yes
Overvoltage category	CAT II 690 V; CAT III 600 V
Display range DC	12 - 690 V
IP Index of Protection	IP 54
Calibration	I1
Number of batteries contained	2
Article no of the battery / rechargeable battery fitted	081551 LR3
Power supply	Battery-powered
Type of product	Voltage tester

## Services

CalibrationVoltage tester Type S	027120 S
DAkkS calibrationVoltage tester Type S	027160 S

## Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
---	------------