

Garant
Clamping toolholder, right-hand, Shank / insert size: 32/12mm

Order data

Order number	255795 32/12
GTIN	4045197799111
Item class	21T

Technical description

Head length L_1	34 mm
suitable indexable insert	RN.. 1207..
Clamp	259035 3
Shank size	32 mm
Functional width L_4	32 mm
Insert size	12 mm
ISO code toolholder	CRSNR/L 3225P12
Shim	259031 43
Shim screw	259025 2
Overall length L	170 mm
Washer for clamp	259041 1
Series	QuickTurn
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	90 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 43	259031 43
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX20	674248 TX20
Clamp unit Type 3	259035 3
Washer for clamp Type 1	259041 1
Shim screw Type 2	259025 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500