



Electronic torque analyser „TruCheck™ Plus“, maximum torque: 25 N·m



Order data

Order number	654475 25
GTIN	5060207562577
Item class	66D

Description

Version:

- **3 user modes: Tracking display (Track), Trigger point sensing (First Peak), Peak value display (Final-Peak).**
- **Easy input of target torque with tolerances.**
- **Units of measure: N·m, lbf·ft, lbf·in.**

Large easy to read LCD display. Data transmission can be performed by an RS232C connecting cable.

Advantage:

3 LEDs for quick an easy visual indication of status.

Supplied with:

RS232C connection cable to PC / printer or network mode and mains adapter, in sturdy plastic case.

Calibration: O4

Torque measuring accuracy: $\pm 1 \%$

Measuring range: 1 - 25 N·m

Display unit width: 175 mm

Display unit height: 64 mm

Display unit depth: 72 mm

Weight: 2.6 kg

Square drive adapter: 1/4 inch

Technical description

Measuring range	1 - 25 N·m
Square drive adapter	1/4 inch
Square drive adapter	3/8 inch
Display unit height	64 mm
Hexagon socket	1/4 inch
Weight	2.6 kg
Display unit depth	72 mm
Display unit width	175 mm
maximum torque	25 N·m
Torque measuring accuracy	± 1 %
Direction of tightening	For right and left-hand tightening
Interface	RS232C interface
Test certificate	Manufacturer's test certificate
Calibration	O4

Services

Calibration Torque analyser / sensor maximum torque 400/2 Nm	018860 400/2
DAkkS calibration Torque analyser / sensor maximum torque 1000/2 Nm	018840 1000/2

Accessories

Software for monitoring torque wrenches	654270
RS232 PC connection cable	654344