

Garant
Clamping toolholder, neutral, Shank / insert size: 32/12mm

Order data

Order number	255798 32/12
GTIN	4045197799159
Item class	21T

Technical description

suitable indexable insert	RN.. 1207..
Functional width L ₄ neutral holders	12.5 mm
Shim screw	259025 2
Overhang L ₁ neutral holders	34 mm
Insert size	12 mm
Overall length L neutral holders	170 mm
Shim	259031 43
Shank size	32 mm
Clamp	259035 3
ISO code toolholder	CRDNN 3225P12
Washer for clamp	259041 1
Series	QuickTurn
Standard	DIN ISO 5610
Application type	neutral
Through-coolant	no
Setting angle κ	45 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim screw Type 2	259025 2
Shim Type 43	259031 43
Clamp unit Type 3	259035 3
Washer for clamp Type 1	259041 1
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX20	674248 TX20
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500