

bimos

Heavy-duty swivel work chair, synthetic leather



Order data

Order number	965384
GTIN	4016849591070
Item class	96B

Description

Version:

Very sturdy and secure swivel work chair with reinforced extra-large star base of aluminium (Ø 740 mm), gas pressure safety spring with steel cover, strengthened chair mechanism.

Backrest steplessly and individually adjustable for height and inclination. Ergonomically shaped seat and backrest. Transport and carrying handle of steel.

Includes armrests. 570 mm clearance between the armrests, adjustable width.

Extra strong padding with 25% thicker foam volume weight, very sturdy and hard-wearing.

With synthetic leather covering

Standard:**DIN 68877****Supplied with:**

Includes 1 set glides and 1 set castors.

Load capacity chair: 160 kg

Height adjustment range with rollers: 490 - 640 mm

Colour of seat material: black

Technical description

Safe working load	160 kg
-------------------	--------

Height adjustment version	Gas pressure spring
Type of height adjustment	Height adjustment lever
Colour of seat material	black
Version	with castors
Load capacity chair	160 kg
Star base Ø	740 mm
Height adjustment range with pads	450 - 600 mm
Height adjustment range with rollers	490 - 640 mm
Type of product	Swivel work chair