



## Mobile compressed air lubrication unit, suitable for container unit: 25kg



### Order data

|              |               |
|--------------|---------------|
| Order number | 084000 25     |
| GTIN         | 8429765410800 |
| Item class   | 08H           |

### Description

#### Version:

Mobile compressed air lubrication unit with trolley for economic and reliable delivery of long-term greases. High delivery quantity, due to transmission ratio 1: 55, together with large diameter suction port and security lubrication hose. Suitable for oils and greases up to consistency class 2, including bio-greases (general-purpose greases).

#### Supplied with:

Grease follower cover, steel dust protection cover, high-pressure grease guns and 4m hose.

#### Note:

The lubrication system is self-lubricating and requires no additional pipe lubricators. The use of a pressure reducer with water separator is recommended.

### Technical description

|                                  |            |
|----------------------------------|------------|
| maximum lubrication pressure     | 400 bar    |
| required compressed air pressure | 3 - 10 bar |
| maximum delivery quantity        | 600 g/min  |
| suitable for container unit      | 25 kg      |

|                         |                    |
|-------------------------|--------------------|
| Internal Ø of container | 300 - 340 mm       |
| Type of product         | Lubrication device |