

**Location device, Type: GMS120****Order data**

Order number	465570 GMS120
GTIN	3165140560108
Item class	46T

Description**Version:**

Reliable location even of buried objects up to 120 mm deep. Three detection modes (plasterboard, metal, live cables) for different applications. Reliable detection of objects, giving a visual and acoustic signal. Precise indication of the object centre. The centre point of the object that is sought can be simply marked using the marking aperture. Large illuminated display
Softgrip surface for a better grip.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Application:

Detectable materials: Ferrous metals, non-ferrous metals, wooden frameworks, live cables.

Supplied with:

Battery No. 081551 6LR61, hand loop, protective bag.

Technical description

Measuring range	120 mm
Detection depth steel	120 mm

Detection depth copper	80 mm
Detection depth live conductors	50 mm
Detection depth wood	38 mm
Weight	270 g
Length	200 mm
Width	85 mm
Height	32 mm
IP Index of Protection	IP 54
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081561 6LR61
Power supply	Battery-powered
Type of product	Location device