




Laser distance meter, Type: GLM80



Order data

| | |
|--------------|---------------|
| Order number | 465560 GLM80 |
| GTIN | 3165140600804 |
| Item class | 46T |

Description

Version:

Laser distance measurement device with robust, shock-resistant casing, splash-proof and dust-proof (IP 54). Illuminated three-row display for optimum legibility. Laser class 2 to IEC 825-1. Simple operation with improved user interface and illuminated display. Plug-in function. The integral 360° inclination sensor shows the inclination of an object when the casing is placed directly on it, thus permitting indirect height measurement.

Standard:

Laser distance measurement device with robust, shock-resistant casing, splash-proof and dust-proof (IP 54). Illuminated three-row display for optimum legibility. Laser class 2 to IEC 825-1. Stand socket thread 1/4 inch. The integral 360° inclination sensor shows the inclination of an object when the casing is placed directly on it, thus permitting indirect height measurement. Create a digital floor plan, import existing floor plans, edit them and export the result together with simple building site dimensioning. Data transfer via Bluetooth®.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Includes protective case. Incl. Li-ion battery, charger + micro-USB cable.

Optional extras:

Measuring stand No. 468558.

IP Index of Protection: IP 54
Measuring accuracy: ± 1.5 mm
Threaded socket for stand: 1/4 in
Range: 80 m
Addition/subtraction: yes
Minimum / maximum measurements: yes
Surface and volume calculations: yes

Technical description

| | |
|--|------------------------------|
| Width | 51 mm |
| indirect measurements (Pythagoras) | yes |
| Length | 111 mm |
| Battery life (measurements) | 25000 |
| Weight | 140 g |
| Surface and volume calculations | yes |
| Range | 80 m |
| Minimum / maximum measurements | yes |
| Clinometer | 360 ° |
| Power supply | Li-ion battery |
| Threaded socket for stand | 1/4 in |
| Addition/subtraction | yes |
| Height | 30 mm |
| Recall last measurements | yes |
| IP Index of Protection | IP 54 |
| Measuring accuracy | ± 1.5 mm |
| Type of rechargeable battery | Lithium-ion |
| Number of rechargeable batteries contained | 1 |
| Power supply | Rechargeable battery-powered |
| Laser class to IEC 825-1 | 2 |
| Type of product | Distance meter |

Accessories

Photography tripod

468558