

**Garant**
**Solid carbide HPC drill plain shank DIN 6535 HA, TiAlN, Ø DC h7: 3mm**

**Order data**

Order number	122690 3
GTIN	4045197596185
Item class	11E

**Description**
**Version:**

**3 guide chamfers** for particularly high accuracy and surface quality at tight hole tolerances.

**Asymmetrical tip geometry** for **very high metal removal rates**. New generation of **innovative high-performance drills for cast iron** in the HPC field.

**Advantage:**

For HPC high performance drilling in castings. **Outstandingly suitable for bainite cast iron (ADI)**.

**Note:**

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

Form HB and HE supplied at the same price as HA.

Form **HB**: order with **No. 122690 + 129100HB** .

Form **HE**: order with **No. 122690 + 129100HE**.

Standard: DIN 6537

Tolerance nominal Ø: h7

Number of cutting edges Z: 2

recommended maximum drilling depth  $L_2$ : 23.5 mm

Tolerance nominal Ø: h7

Overall length L: 66 mm

Shank Ø  $D_s$ : 6 mm

Feed f in GJS ADI > 800 N/mm<sup>2</sup>: 0.16 mm/rev.

**Technical description**

Feed f in GJS ADI > 800 N/mm <sup>2</sup>	0.16 mm/rev.
Flute length $L_c$	28 mm
Number of cutting edges Z	2

Shank tolerance	h6
Nominal $\varnothing D_c$	3 mm
Tolerance nominal $\varnothing$	h7
Shank $\varnothing D_s$	6 mm
Overall length L	66 mm
Standard	DIN 6537
recommended maximum drilling depth $L_2$	23.5 mm
Coating	TiAlN
Tool material	Solid carbide
Version	6xD
Point angle	135°
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	white
Type of product	Jobber drill

## User data

	Suitability	$V_c$	ISO code
GG	suitable	110 m/min	K
GGG	suitable	90 m/min	K
GJS, ADI > 800N/mm <sup>2</sup>	suitable	70 m/min	K
wet maximum	suitable		
wet minimum	suitable		

## Services

Shank grinding Type HE	129100 HE
Shank grinding Type HB	129100 HB

