




## Weldon element with compensation, short, For nominal $\varnothing$ d: 11 mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 335720 11     |
| GTIN         | 4045197801531 |
| Item class   | 32P           |

### Description

#### Version:

Plain toolholder, hardened and ground with **quick-release coupling**. Internal square to take taps and transmit the torque. Clamping mechanism prevents the tap being pulled out. Tensile/compression compensation each of 0.2 mm by means of compensation element. Clamping of the Weldon element either by means of the drive flats or the compensation element.

#### Advantage:

- **Attractively priced solution.**
- **Sturdy, slim version.**
- **Variation in the clamping and overhang lengths.**

#### Application:

To take taps and others in a Weldon arbor.

#### Optional extras:

Compensation element No. 335730.

#### Note:

Minimum compensation function **only** in combination with No. 300415 and 335730. The standard Weldon chuck permits only rigid clamping, see No. 335740.

### Technical description

|                          |       |
|--------------------------|-------|
| Clamping range d         | 11 mm |
| External $\varnothing$ D | 20 mm |
| Adjustment travel V      | 10 mm |
| Overhang A               | 52 mm |

|                  |              |
|------------------|--------------|
| Overall length L | 50 mm        |
| Type of product  | Tapping head |

---

## Accessories

|  |              |
|--|--------------|
| Compensation element Clamping range d 11-12 mm | 335730 11-12 |
|--|--------------|