

**Garant**
**Clamping toolholder, left-hand, Shank / insert size: 25/12mm**

**Order data**

Order number	255796 25/12
GTIN	4045197799128
Item class	21T

**Technical description**

Shim	259031 43
Shim screw	259025 2
Overall length L	150 mm
Clamp	259035 3
Functional width L <sub>4</sub>	32 mm
suitable indexable insert	RN.. 1207..
ISO code toolholder	CRSNR/L 2525M12
Shank size	25 mm
Insert size	12 mm
Head length L <sub>1</sub>	34 mm
Washer for clamp	259041 1
Series	QuickTurn
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	90 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Washer for clamp Type 1	259041 1
Shim screw Type 2	259025 2
Clamp unit Type 3	259035 3
Shim Type 43	259031 43
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX20	674248 TX20
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500