



MultiMaster FMM 350 Q, Type: 72295262



Order data

Order number	077814 72295262
GTIN	4014586884691
Item class	03F

Description

Version:

Market-leading oscillating tools in three different performance classes (SuperCut, MultiMaster, MultiTalent) in a new version with **Starlock tool arbor** (improved torque transmission of up to 35 % greater rate of progression of the work).

- **Virtually unlimited application possibilities (sawing, grinding, scraping, cutting, rasping) due to the oscillating mode of movement (low generation of dust).**
- **Stepless electronic speed control for optimum working.**
- **Very high quality and stability thanks to the metal gearbox and use of ball bearings and needle bearings throughout.**
- **Optimum handling due to ergonomic design with soft-grip inlays and low weight.**

MultiMaster – powerful, universal orbital machines.

- **Extremely smooth cutting action.**
- **Anti-vibration system with robust motor (housing decoupling).**

Power supply adapters with convenient cable length (5 m). **QuickStart** – With basic equipment.

Standard:

MultiMaster – powerful, universal orbital machines.

- **Very smooth cutting action.**
- **Anti-vibration system with robust motor (housing decoupling).**
- **Virtually unlimited application possibilities (sawing, grinding, scraping, cutting, rasping) due to the oscillating mode of movement (low generation of dust).**
- **QuickIN quick-release clamping system (quicker tool change times, no wrench required)**
- **Stepless electronic speed control for optimum working.**

- **Very high quality and stability thanks to the metal gearbox and use of ball bearings and needle bearings throughout.**
- **Optimum handling due to ergonomic design with soft-grip inlays and low weight.**

Supplied with:

1 toolbox set "**QuickStart**" with 1 abrasive plate, 3 each discs (K60, 80, 120, 180), 1 fixed spatula, 1 universal E-Cut saw blade (44 mm), 1 E-Cut long-life saw blade (65 mm), 1 HSS segmented saw blade.

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

Packaging: Carrying case

Manufacturer's designation: FMM 350 QSL QuickStart

Power consumption: 350 W

Toolholder: StarlockPlus, Starlock

Speed of oscillation: 10000 - 19500 rpm

Amplitude (oscillation movement): 2 × 1.7 degrees

Width across grinding plate head: 80 mm

Technical description

Weight	1.4 kg
Power consumption	350 W
Speed of oscillation	10000 - 19500 rpm
Width across grinding plate head	80 mm
Cable length	5 m
Manufacturer's designation	FMM 350 QSL QuickStart
Toolholder	StarlockPlus, Starlock
Amplitude (oscillation movement)	2 × 1.7 degrees
Packaging	Carrying case