



Power clamp adjustable long, Type: 2



Order data

Order number	370091 2
GTIN	4020772004651
Item class	35A

Description

Version:

- Clamping force 30 or 49 kN with tightening torque of approx. 100 Nm.
- Forged clamping element of alloy heat-treatable steel, black galvanised.
- Steplessly adjustable height and length.
- Low installed height.

Supplied with:

- Base element and carrier.
- T-nut DIN 508 with T-bolt strength class 12.9.

Optional extras:

Pressure pads No. 370095.

Technical description

Fastening screw G	M16
T-slot width	18 mm
Width across flats AF	8 mm
with height element	no

Clamping height h-H	6 - 68 mm
B	54 mm
B ₁	18 mm
A	36 mm
A ₁	85 mm
Clamping force	30 kN
Fastening screw G ₁	M16
L	135 mm
Adjustment travel V	16 - 114 mm
Type	764CC
Type of product	Sliding clamp

Accessories

Pressure pad, stainless steel Type DR	370095 DR
Pressure pad, stainless steel Type DG	370095 DG
Spacer elementlong for type 1/2	370093 1/2