



Power clamp adjustable long, Type: 3



Order data

Order number	370091 3
GTIN	4020772004668
Item class	35A

Description

Version:

- Clamping force 30 or 49 kN with tightening torque of approx. 100 Nm.
- Forged clamping element of alloy heat-treatable steel, black galvanised.
- Steplessly adjustable height and length.
- Low installed height.

Supplied with:

- Base element and carrier.
- T-nut DIN 508 with T-bolt strength class 12.9.

Optional extras:

Pressure pads No. 370096.

Technical description

T-slot width	18 mm
Fastening screw G	M16
Width across flats AF	10 mm
with height element	no

Clamping height h-H	5 - 80 mm
B	60 mm
B ₁	20 mm
A	42 mm
A ₁	105 mm
Clamping force	43 kN
Fastening screw G ₁	M20
L	155 mm
Adjustment travel V	16 - 134 mm
Type	764CC
Type of product	Sliding clamp

Accessories

Spacer element long for type 3	370093 3
Pressure pad, stainless steel Type DR	370096 DR
Pressure pad, stainless steel Type DG	370096 DG