

Garant

**Solid carbide HPC drill type FS Weldon shank DIN 6535 HB, TiAlN, Ø DC h7:
13,8 mm**


Order data

Order number	122675 13,8
GTIN	4045197398413
Item class	11E

Description
Version:

Particularly strong due to strengthened core and **special profile**. Special point geometry.
High concentricity and **long tool life**.

Precision drilling qualities.

Recommendation:
Maximum drilling depth:

Flute length (see table) less 1.5×nominal Ø.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Standard: DIN 6537

Tolerance nominal Ø: h7

Number of cutting edges Z: 2

Semi-Standard: yes

Tolerance nominal Ø: h7

recommended maximum drilling depth L_2 : 56.3 mm

Overall length L: 124 mm

Shank Ø D_s : 14 mm

Feed f in titanium > 850 N/mm²: 0.16 mm/rev.

Technical description

Shank tolerance	h6
Feed f in titanium > 850 N/mm ²	0.16 mm/rev.
Flute length L_c	77 mm
Nominal Ø D_c	13.8 mm

Number of cutting edges Z	2
Tolerance nominal \varnothing	h7
Shank $\varnothing D_s$	14 mm
Overall length L	124 mm
Standard	DIN 6537
recommended maximum drilling depth L_2	56.3 mm
Semi-Standard	yes
Coating	TiAlN
Tool material	Solid carbide
Drill depth up to	6xD
Type	FS
Point angle	140 degrees
Shank	DIN 6535 HB to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Colour ring	pink
Type of product	Jobber drill