

**Garant****3-way extension base for centring vice, for type: 80/120****Order data**

Order number	360156 80/120
GTIN	4045197801937
Item class	310

**Description****Version:**

Clamping of the centring vice on the three-way extension base via clamping claws. Double slot per clamping side, meaning the centring vices can be turned by 90°. Secured via GARANT ZeroClamp zero point clamping system (holes 18M16) or via T-nuts directly on to the machine table.

**Material:**

High-tensile aluminium, hard anodised.

**Suitable for:**

Centring vice No. 360133.

**Supplied with:**

Including 6 T-nuts for alignment

**Note:**

Use clamping set No. 363102 size 80 to install the GARANT Xtric No. 363000 size 50 or size 80.

**Technical description**

Ø d	400 mm
Angle α	45 degrees
Slot width n H7	20 mm
Height h	140 mm
Type of product	Vice accessories

---

## Accessories

Alignment and clamping strip set, Xtric Type 80	363102 80
Centring vice basic device Xtric Type 80M	363000 80M