

**Swing clamp, without handle, Type: 30L****Order data**

Order number	370085 30L
GTIN	2050001884350
Item class	37K

Description**Version:**

- **"One Touch" swing clamp with axial clamping stroke (H1/H2) by lever movement (right/left).**
- **Body of hardened and tempered steel; burnished.**
- **Even clamping force over the component.**
- **Removable handle, so few interference contours.**

Application:

- **For quickly clamping and releasing individual components.**
- **For light duty machining work.**

Note:

Screw-in handles with torque limitation available on request.

maximum clamping force: 800 N

max. hand force grip: 150 N

Technical description

Dimension E	18 mm
-------------	-------

Height H	57.5 mm
Type	30L
Thread M	M6
L ₁	32 mm
L ₂	15 mm
B ₁	14 mm
Clamping height H ₁ min.	31.4 mm
Clamping height H ₁ max.	32.6 mm
maximum clamping force	800 N
max. hand force grip	150 N
B	30 mm
L ₃	25 mm
Thread M ₁	M4
Type of product	Jig clamping system