



Swing clamp, without handle, Type: 40L



Order data

Order number	370085 40L
GTIN	2050001872739
Item class	37K

Description

Version:

- "One Touch" swing clamp with axial clamping stroke (H1/H2) by lever movement (right/left).
- Body of hardened and tempered steel; burnished.
- Even clamping force over the component.
- Removable handle, so few interference contours.

Application:

- For quickly clamping and releasing individual components.
- For light duty machining work.

Note:

Screw-in handles with torque limitation available on request.

maximum clamping force: 1200 N

max. hand force grip: 200 N

Technical description

L ₂	20 mm
----------------	-------

Thread M	M8
L ₁	40 mm
Height H	78.1 mm
Dimension E	25 mm
Type	40L
B ₁	16 mm
Clamping height H ₁ min.	44.1 mm
Clamping height H ₁ max.	45.9 mm
maximum clamping force	1200 N
max. hand force grip	200 N
B	40 mm
L ₃	32 mm
Thread M ₁	M6
Type of product	Jig clamping system