



Swing clamp, with handle, Type: 40L



Order data

Order number	370086 40L
GTIN	2050001878618
Item class	37K

Description

Version:

- **“One Touch” swing clamp with axial clamping stroke (H1/H2) by lever movement (right/left).**
- **Body of hardened and tempered steel; burnished.**
- **Even clamping force over the component.**
- **Removable handle, so few interference contours.**

Application:

- **For fast clamping / releasing of individual components.**
- **For light machining work.**

Note:

Screw-in handles with torque limitation available on request.
 maximum clamping force: 1200 N
 max. hand force grip: 200 N

Technical description

L ₁	40 mm
Dimension E	25 mm
Height H	78.1 mm

B ₁	16 mm
Type	40L
Thread M	M8
L ₂	20 mm
Clamping height H ₁ min.	44.1 mm
Clamping height H ₁ max.	45.9 mm
maximum clamping force	1200 N
max. hand force grip	200 N
B	40 mm
L ₃	32 mm
Thread M ₁	M6
Type of product	Jig clamping system