



Mobile compressed air lubrication unit, suitable for container unit: 15/18kg



Order data

Order number	084000 15/18
GTIN	8429765410794
Item class	08H

Description

Version:

Mobile compressed air lubrication unit with trolley for economic and reliable delivery of long-term greases. High delivery quantity, due to transmission ratio 1: 55, together with large diameter suction port and security lubrication hose. Suitable for oils and greases up to consistency class 2, including bio-greases (general-purpose greases).

Supplied with:

Grease follower cover, steel dust protection cover, high-pressure grease guns and 4m hose.

Note:

The lubrication system is self-lubricating and requires no additional pipe lubricators. The use of a pressure reducer with water separator is recommended.

Technical description

Internal Ø of container	255 - 282 mm
required compressed air pressure	3 - 10 bar
maximum lubrication pressure	400 bar
maximum delivery quantity	600 g/min

suitable for container unit	15 / 18 kg
Type of product	Lubrication device