



Voltage tester, Type: 750-2



Order data

Order number	473210 750-2
GTIN	4029547013904
Item class	47B

Description

Version:

Sturdy plastic casing and ergonomic handle shape with non-slip ring for safe working with no risk of slipping. **Clear 360° display** with fibre optic cable. **Integral torch** for illuminating the measurement area.

Function:

IP64: Protected against splashed water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Application:

For professional multi-stage voltage, continuity, and polarity testing. Suitable for working on electrical systems, industrial systems, maintenance, servicing (troubleshooting), With load switching (30 mA RCB trip by push button).

Standard:

DIN EN 61243-3 und CAT III

Supplied with:

Batteries No. 081561 size LR3, test prod protection and measurement prod extensions.

Technical description

Display range AC	12 - 690 V
Illumination of probe points	yes
Overvoltage category	CAT III 1000 V; CAT IV 600 V
Three phase sequence testing	100 – 690 V
Display range DC	12 - 690 V
Phase testing	100 – 690 V
Continuity testing	acoustic / LED up to 500 kΩ
IP Index of Protection	IP 64
FI/RCD protective switch test current	yes
Calibration	I1
Number of batteries contained	2
Article no of the battery / rechargeable battery fitted	081551 LR3
Power supply	Battery-powered
Type of product	Voltage tester

Services

Calibration Voltage tester Type S	027120 S
DAkkS calibration Voltage tester Type S	027160 S

Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
---	------------