

**Electronic end cutter, mirror-polished, 27° angled, FW, overall length: 115mm****Order data**

Order number	726960 115
GTIN	4003773017844
Item class	73F

Description**Version:**

Mirror polished, therefore no faults in the circuit due to peeling chrome plate. Sturdy box joint with zero play. Low-friction double spring for smooth and gentle opening. Multi-component grips, blue/red.

Application:

For making precision cuts, e.g. in electronics and precision mechanisms.

Standard:**DIN ISO 9654****Material:**

Ball-bearing steel, cutting edges induction hardened.

Technical description

Cutter length	12 mm
overall length	115 mm
Head width	10.5 mm
Cutting capacity copper wire up to Ø	1.5 mm
Cutting chamfer	fine bevel
Joint	box joint, free of play
Head	27° angled

Standard	DIN ISO 9654
Handle	Multi-component covering
Manufacturing process	Cutting edges induction hardened (approx. 56 HRC)
Material	Special quality tool steel, drop-forged, oil-hardened
Surface	mirror polished
Product name attribute	FW
with return spring	yes
Type of product	Cutting pliers