

Garant

Solid carbide HPC drill plain shank DIN 6535 HA, TiAlN, Ø DC h7: 13,5mm



Order data

Order number	122690 13,5
GTIN	4045197597236
Item class	11E

Description

Version:

3 guide chamfers for particularly high accuracy and surface quality at tight hole tolerances.

Asymmetrical tip geometry for **very high metal removal rates**. New generation of **innovative high-performance drills for cast iron** in the HPC field.

Advantage:

For HPC high performance drilling in castings. **Outstandingly suitable for bainite cast iron (ADI)**.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Form HB and HE supplied at the same price as HA.

Form **HB**: order with **No. 122690 + 129100HB** .

Form **HE**: order with **No. 122690 + 129100HE**.

Standard: DIN 6537

Tolerance nominal Ø: h7

Number of cutting edges Z: 2

recommended maximum drilling depth L_2 : 56.8 mm

Tolerance nominal Ø: h7

Overall length L: 124 mm

Shank Ø D_s : 14 mm

Feed f in GJS ADI > 800 N/mm²: 0.35 mm/rev.

Technical description

Shank tolerance	h6
Number of cutting edges Z	2
Flute length L_c	77 mm

Feed f in GJS ADI > 800 N/mm ²	0.35 mm/rev.
Nominal Ø D _c	13.5 mm
Tolerance nominal Ø	h7
Shank Ø D _s	14 mm
Overall length L	124 mm
Standard	DIN 6537
recommended maximum drilling depth L ₂	56.8 mm
Coating	TiAlN
Tool material	Solid carbide
Version	6×D
Point angle	135 °
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	white
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
GG	suitable	110 m/min	K
GGG	suitable	90 m/min	K
GJS, ADI > 800N/mm ²	suitable	70 m/min	K
wet maximum	suitable		
wet minimum	suitable		

Services

Shank grinding Type HB	129100 HB
Shank grinding Type HE	129100 HE

