

Garant**Diamond grinding point set, 10 pieces D126, D, Number of grinding points: 10****Order data**

| | |
|--------------|---------------|
| Order number | 552810 10 |
| GTIN | 4045197803139 |
| Item class | 51E |

Description**Version:**

Assortment of grinding points in the most popular shapes and sizes. Shank \varnothing 3 mm.

Application:

Diamond grinding points for **carbide, technical ceramic, grey cast iron and spheroidal graphite iron, glass, CRP/GRP.**

Supplied with:

1 each grinding point.

Cylinder No. 552500 size 1; 2; 3; 5;

Ball No. 552600 size 1; 2; 3; 4; 6;

Gothic arch No. 552700 G0307.

Technical description

| | |
|---------------------------|---------|
| Shank \varnothing | 3 mm |
| Number of grinding points | 10 |
| Grinding media | Diamond |
| Grinding medium code | D |

Type of product

Grinding point

User data

| | Suitability | V _c | ISO code |
|--------------|---|----------------|----------|
| Carbide (HM) | suitable | 15-20 m/s | |
| Plastic, GRP | suitable | 15-20 m/s | |
| Stone | suitable | 15-20 m/s | |
| wet maximum | suitable | | |
| dry | suitable only under restricted conditions | | |

Accessories

| | |
|---|--------------|
| Diamond grinding pointgalvanic D126 Shape G0307 | 552700 G0307 |
| Diamond grinding pointgalvanic D126 Head Ø 1 mm | 552600 1 |
| Diamond grinding pointgalvanic D126 Head Ø 2 mm | 552600 2 |
| Diamond grinding pointgalvanic D126 Head Ø 6 mm | 552600 6 |
| Diamond grinding pointgalvanic D126 Head Ø 1 mm | 552500 1 |
| Diamond grinding pointgalvanic D126 Head Ø 5 mm | 552500 5 |
| Diamond grinding pointgalvanic D126 Head Ø 3 mm | 552600 3 |
| Diamond grinding pointgalvanic D126 Head Ø 3 mm | 552500 3 |
| Diamond grinding pointgalvanic D126 Head Ø 2 mm | 552500 2 |
| Diamond grinding pointgalvanic D126 Head Ø 4 mm | 552600 4 |