

Garant**CBN grinding point set, 10 pieces B126, CBN, Number of grinding points: 10****Order data**

Order number	552820 10
GTIN	4045197803146
Item class	51E

Description**Version:**

Assortment of grinding points in the most popular shapes and sizes. Shank \varnothing 3 mm.

Application:

For **all hardened, tempered and high-alloy steels.**

Supplied with:

1 each grinding point.

Cylinder No. 552550 size 1; 2; 3; 4; 5; Ball No. 552650 size 1; 2; 3; 4; 6.

Technical description

Shank \varnothing	3 mm
Number of grinding points	10
Grinding media	Cubic Boron Nitride
Grinding medium code	CBN
Type of product	Grinding point

User data

	Suitability	V _c	ISO code
Steel < 1400 N/mm ²	suitable	20-30 m/s	P
Steel < 55 HRC	suitable	20-30 m/s	H
Steel < 60 HRC	suitable	20-30 m/s	H
Steel < 67 HRC	suitable	20-30 m/s	H
INOX	suitable	20-30 m/s	
Ti	suitable	20-30 m/s	
GG(G)	suitable	20-30 m/s	K
wet maximum	suitable		
dry	suitable only under restricted conditions		

Accessories

CBN grinding pointsgalvanic B126 Head Ø 5 mm	552550 5
CBN grinding pointsgalvanic B126 Head Ø 4 mm	552550 4
CBN grinding pointsgalvanic B126 Head Ø 6 mm	552650 6
CBN grinding pointsgalvanic B126 Head Ø 1 mm	552550 1
CBN grinding pointsgalvanic B126 Head Ø 4 mm	552650 4
CBN grinding pointsgalvanic B126 Head Ø 2 mm	552650 2
CBN grinding pointsgalvanic B126 Head Ø 3 mm	552550 3
CBN grinding pointsgalvanic B126 Head Ø 1 mm	552650 1
CBN grinding pointsgalvanic B126 Head Ø 3 mm	552650 3
CBN grinding pointsgalvanic B126 Head Ø 2 mm	552550 2