

Garant**RC.X 1003, Grade: HB7020**

Order data

Order number	260640 HB7020
GTIN	4045197801845
Item class	21G

Description

RC.X 1003 HB7020 Chip breaker: SM
Tolerance: M
Cutting depth a_p : 0.5 - 2 mm
Feed f : 0.1 - 0.3 mm/rev.
Cutting speed v_c main application: 120 - 350 m/min

Technical description

Main application	P
Grade	HB7020
Cutting depth a_p	0.5 - 2 mm
Feed f	0.1 - 0.3 mm/rev.
Cutting conditions	slightly interrupted
Chip breaker	SM
Cutting speed v_c main application	120 - 350 m/min

Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	RCMX 1003
Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning