

**Two-speed power drill, Type: 720555****Order data**

Order number	075150 720555
GTIN	4014586882567
Item class	03F

**Description****Version:**

- **Compact 2-speed power drill for drilling, countersinking, tapping, and screwdriving.**
- **Stepless electronic speed control for gentle starts to drilling and screwdriving.**
- **Integral switch with clockwise / anticlockwise switch for ease of use.**

Additional serrated handle for secure holding (positive grip).

**Advantage:**

Stepless electronic speed control.

**Supplied with:**

Quick-clamping drill chuck with locking force safety device, 1 additional handle.

**Note:**

Suitable jobber drills can be found from No. 114000.

**Technical description**

Chuck clamping range	1.5 - 13 mm
Weight	2 kg
maximum twist drill size Ø in wood 1st speed	37 mm
maximum twist drill size Ø in steel 2nd speed	10 mm
Maximum twist drill size Ø in steel 1st speed	13 mm
maximum vibration to EN	< 2.5 m/s <sup>2</sup>

Manufacturer's designation	BOP 13-2
Drill chuck adapter	1/2 inch – 20 UNF
Power consumption	550 W
maximum twist drill size Ø in wood 2nd speed	27 mm
Speed range 1st speed	0 - 680 min <sup>-1</sup>
Speed range 2nd speed	0 - 2200 min <sup>-1</sup>
Power supply	Mains operated
Suitable for material	Steel
Type of product	Drill