


**HOLEX****Flap wheel (A), 150 grit, Head Ø×head width: 3/30X10mm****Order data**

Order number	554400 3/30X10
GTIN	4045197803375
Item class	52E

**Description****Version:**

Flap strips bonded on to the shank of the tool.  
Abrasive strips covered with **Aluminium Oxide (A)**.

**Application:**

Primarily for finish grinding and polishing tasks on larger radii in tool and mould making, for vessel and machine fabrication. The abrasive strips adapt to the contours of the component.

**Technical description**

maximum speed	18000 min <sup>-1</sup>
recommended speed	16000 min <sup>-1</sup>
Grit	150
Shank Ø	3 mm
Head Ø	30 mm
Head width	10 mm
Grinding media	Aluminium Oxide grit (A)
Grinding medium code	A
Product name attribute	150 grit

Type of product

Flap wheel

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
dry	suitable		