BOSCH

"CYL-3" carbide masonry drill, Drill Ø: 5 mm

COLORON as man

Order data

| Order number | 786005 5 |
|--------------|---------------|
| GTIN | 3165140186704 |
| Item class | 76K |

Description

Version:

Drill tipped with hard and tough carbide inserts and brazed at high temperature. Asymmetrical flute profile for good transport of drill dust.

Hammer and rotary bits with strong carbide cutter tip.

Application:

Primarily for **drilling dowel holes with hammer drills** in concrete, masonry, natural and synthetic stone.

Also for rotary drilling in hard and soft wood, plastics, acrylic and ceramic. Also suitable for drilling hardened steel due to corrected cutting edge.

Shank: Plain shank Flute length: 50 mm overall length: 85 mm Shank Ø: 5 mm

Technical description

| Flute length | 50 mm |
|---------------------------|----------|
| overall length | 85 mm |
| Drill Ø | 5 mm |
| Number of cutting edges Z | 2 |
| Shank Ø | 5 mm |
| Tool material | Carbide |
| Standard | ISO 5468 |
| Standard | DIN 8039 |

| Use with impact / without impact | Impact drilling |
|----------------------------------|-----------------|
| Shank | Plain shank |
| Type of product | Masonry drill |