

**Flap wheel Fleece (SiC), medium, Head Ø×head width: 80X50mm****Order data**

| | |
|--------------|---------------|
| Order number | 554972 80X50 |
| GTIN | 4045197804006 |
| Item class | 52E |

Description**Version:**

Flap strips of fleece around the shank of the tool. Shank Ø 6 mm.

The sharp-edged silicon carbide grit (SiC) provides aggressive grinding characteristics and a **slightly lustrous finish**.

Application:

For removal of dirt and oxide layers on metals as well as for matt finishing of Cr-Ni, other stainless steels, and also non-ferrous metals.

Technical description

| | |
|-------------------|------------------------|
| Shank Ø | 6 mm |
| recommended speed | 4000 min ⁻¹ |
| Head Ø | 80 mm |
| maximum speed | 7000 min ⁻¹ |
| Head width | 50 mm |
| Grinding media | Silicon carbide |

| | |
|------------------------|------------|
| Grinding medium code | SiC |
| Grit equivalent | 180 |
| Grit designation | medium |
| Product name attribute | medium |
| Type of product | Flap wheel |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable only under restricted conditions | | |
| INOX | suitable | | |
| Ti | suitable | | |
| GG(G) | suitable | | |
| CuZn | suitable | | |
| Plastic, GRP | suitable | | |
| Stone | suitable only under restricted conditions | | |
| Paint | suitable only under restricted conditions | | |
| dry | suitable | | |