



## "CYL-3" carbide masonry drill, Drill Ø: 18 mm



### Order data

Order number	786005 18
GTIN	3165140186841
Item class	76K

### Description

#### Version:

Drill tipped with hard and tough carbide inserts and brazed at high temperature. Asymmetrical flute profile for good transport of drill dust.

**Hammer and rotary bits** with strong carbide cutter tip. With recessed shank.

#### Application:

Primarily for **drilling dowel holes with hammer drills** in concrete, masonry, natural and synthetic stone.

Also for rotary drilling in hard and soft wood, plastics, acrylic and ceramic. Also suitable for drilling hardened steel due to corrected cutting edge.

Shank: Plain shank

Flute length: 100 mm

overall length: 160 mm

Shank Ø: 12.3 mm

### Technical description

overall length	160 mm
Number of cutting edges Z	2
Drill Ø	18 mm
Flute length	100 mm
Shank Ø	12.3 mm
Tool material	Carbide
Standard	ISO 5468
Standard	DIN 8039

Use with impact / without impact	Impact drilling
Shank	Plain shank
Type of product	Masonry drill