




## “CYL-9” carbide-tipped multi-purpose drill, Drill Ø: 10 mm



### Order data

Order number	787005 10
GTIN	3165140044875
Item class	76K

### Description

#### Version:

Carbide tip **with ground point and multi-purpose cutter angle. The centrally ground chisel edge** ensures accurate spot drilling also on hard surfaces. Shank of annealed special steel.

#### Application:

For drilling various materials, in a single operation:

- **Bricks, porous concrete, lightweight materials, plastics.**
- **Tiles, ceramics, marble, glass**
- **Reinforcing bars in concrete.**

#### Note:

- **Caution: only for rotary use (without hammer action!)**
- **Faster drilling and more holes per battery charge than with hammer drill bits.**

Shank: Plain shank

Flute length: 80 mm

overall length: 120 mm

### Technical description

Number of cutting edges Z	2
Drill Ø	10 mm
overall length	120 mm
Flute length	80 mm
Tool material	Carbide
Use with impact / without impact	not for impact drilling
Shank	Plain shank
Type of product	Multi-purpose drill

