

Garant

Solid carbide HPC drill plain shank DIN 6535 HA, TiAlN, Ø DC h7: 11,5mm



Order data

Order number	122690 11,5
GTIN	4045197597199
Item class	11E

Description

Version:

3 guide chamfers for particularly high accuracy and surface quality at tight hole tolerances.

Asymmetrical tip geometry for **very high metal removal rates**. New generation of **innovative high-performance drills for cast iron** in the HPC field.

Advantage:

For HPC high performance drilling in castings. **Outstandingly suitable for bainite cast iron (ADI)**.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Form HB and HE supplied at the same price as HA.

Form **HB**: order with **No. 122690 + 129100HB**.

Form **HE**: order with **No. 122690 + 129100HE**.

Standard: DIN 6537

Tolerance nominal Ø: h7

Number of cutting edges Z: 2

recommended maximum drilling depth L_2 : 53.8 mm

Tolerance nominal Ø: h7

Overall length L: 118 mm

Shank Ø D_s : 12 mm

Feed f in GJS ADI > 800 N/mm²: 0.29 mm/rev.

Technical description

Shank tolerance	h6
Nominal Ø D_c	11.5 mm
Feed f in GJS ADI > 800 N/mm ²	0.29 mm/rev.

Flute length L_c	71 mm
Number of cutting edges Z	2
Tolerance nominal \varnothing	h7
Shank $\varnothing D_s$	12 mm
Overall length L	118 mm
Standard	DIN 6537
recommended maximum drilling depth L_2	53.8 mm
Coating	TiAlN
Tool material	Solid carbide
Version	6xD
Point angle	135°
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	white
Type of product	Jobber drill

User data

	Suitability	V_c	ISO code
GG	suitable	110 m/min	K
GGG	suitable	90 m/min	K
GJS, ADI > 800N/mm ²	suitable	70 m/min	K
wet maximum	suitable		
wet minimum	suitable		

Services

Shank grinding Type HE	129100 HE
Shank grinding Type HB	129100 HB

