

Garant**Micro boring-out insert, internal, right-hand, L1 = 30 mm, Ø Dmin: 6,2mm**

Order data

Order number	270520 6,2
GTIN	4045197802309
Item class	21I

Description

Application:

For cutter holder No. 270200 – 270204.

Technical description

Shank Ø d	6 mm
Minimum Ø D _{min}	6.2 mm
Radius R	0.2 mm
maximum cutting depth t _{max}	0.5 mm
Tip centre offset L ₃	2.95 mm
Feed f in stainless steel < 900 N/mm ²	0.025 mm/rev.
Feed f in steel < 1100 N/mm ²	0.050 mm/rev.
Feed f in stainless steel > 900 N/mm ²	0.025 mm/rev.
Series	Micro
Overhang L ₁	30 mm
Product name attribute	L ₁ = 30 mm
Type of product	Cutter insert for turning

User data

	Suitability	V_c	ISO code
Alu plastics	suitable only under restricted conditions	250 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	200 m/min	N
Alu > 10% Si	suitable only under restricted conditions	200 m/min	N
Steel < 500 N/mm ²	suitable	160 m/min	P
Steel < 750 N/mm ²	suitable	150 m/min	P
Steel < 900 N/mm ²	suitable	150 m/min	P
Steel < 1100 N/mm ²	suitable	80 m/min	P
Steel < 1400 N/mm ²	suitable	60 m/min	P
Steel < 55 HRC	suitable only under restricted conditions	30 m/min	H
INOX < 900 N/mm ²	suitable	90 m/min	M
INOX > 900 N/mm ²	suitable	60 m/min	M
Ti > 850 N/mm ²	suitable only under restricted conditions	30 m/min	S
GG(G)	suitable	90 m/min	K
CuZn	suitable	150 m/min	N
continuous	suitable		
irregular	suitable only under restricted conditions		
interrupted	suitable only under restricted conditions		
wet maximum	suitable		