

**Burr Z steel – coarse, Carbide, Type: A1225****Order data**

Order number	540740 A1225
GTIN	4045197804730
Item class	52D

**Description****Version:**

**The innovative tooth geometry permits very high metal removal rates** combined with **smooth cutting and good guidance accuracy**. The optimised chip formation (no pointed chips) ensures good surface quality. Shank  $\varnothing$  6 mm.

**Application:**

Optimised for **use on steel and steel castings**.

**Technical description**

Overall length	70 mm
Shape description	cylindrical
Toothing grit designation	coarse
Tooth type abbreviation	Z steel
Shape	A1225
Head $\varnothing$	12.7 mm

Shank Ø	6 mm
Head length	25 mm
Series	Tooth configuration Z steel
Tool material	Carbide
Type of product	Burr

### User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
GG(G)	suitable		