

**Garant****Mini burr Z9 very coarse (NF/Alu), Carbide, Type: C0313****Order data**

Order number	546908 C0313
GTIN	4045197804976
Item class	51D

**Description****Version:**

**GARANT** burrs are manufactured from highest quality carbide with high wear-resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Carbide mini burr with shank Ø 3 mm.

**Application:**

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

**Technical description**

Shape	C0313
Overall length	40 mm
Shape description	Ball nose
Shank Ø	3 mm

Toothing grit designation	very coarse (NF/Alu)
Tooth type abbreviation	Z9
Head Ø	3 mm
Head length	13 mm
Series	#Tooth configuration Z9
Tool material	Carbide
Type of product	Burr

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
CuZn	suitable		
Plastic, GRP	suitable only under restricted conditions		