

**Garant****Mini burr Z9 very coarse (NF/Alu), Carbide, Type: D0403****Order data**

Order number	546908 D0403
GTIN	4045197804983
Item class	51D

**Description****Version:**

**GARANT** burrs are manufactured from highest quality carbide with high wear-resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Carbide mini burr with shank  $\varnothing$  3 mm.

**Application:**

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

**Technical description**

Toothing grit designation	very coarse (NF/Alu)
Tooth type abbreviation	Z9
Shank $\varnothing$	3 mm
Head $\varnothing$	4 mm
Shape	D0403
Shape description	Ball
Overall length	34 mm
Head length	3 mm
Series	#Tooth configuration Z9
Tool material	Carbide

Type of product

Burr

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Alu Mg	suitable		
CuZn	suitable		
Plastic, GRP	suitable only under restricted conditions		