

**Combidisc® grinding disc Diamond, Ø 50.8 mm, Grit: 220****Order data**

Order number	554033 220
GTIN	4007220750506
Item class	55G

**Description****Version:**

The Roloc™, Combidisc® CDR **quick-change system** with a plastic thread permits safe abrasive tool changing "with a single twist of the wrist" in a very short time.

Grinding discs with diamond grit (D) for **extremely hard materials** such as carbide, glass, ceramic, CRP/GRP and wear protection coatings (such as enamel). Use on hard or medium-hard backing pads.

**Application:**

For efficient abrasion of small areas, even with changing contours. Reduced tool changing times save costs on multi-stage operations.

**Note:**

**Roloc™ bristle discs** can be found from No. 573510 onwards.

**Technical description**

Grit	220
Disc Ø	50.8 mm
equivalent to grit size	76 µm
Grinding media	Diamond
Grinding medium code	D

Product name attribute	Ø 50.8 mm
maximum speed	7500 min <sup>-1</sup>
Type of product	Grinding wheel

## User data

	Suitability	V <sub>c</sub>	ISO code
Carbide (HM)	suitable		
Ti	suitable		
Plastic, GRP	suitable		
Stone	suitable		
dry	suitable		

## Accessories

Rubber backing pad shank Ø 6 mm hard External Ø 50 mm	554089 50
Rubber backing pad shank Ø 6 mm medium External Ø 50 mm	554092 50
Rubber backing pad shank Ø 6 mm medium hard External Ø 50 mm	554093 50
Plastic backing pad shank Ø 6 mm External Ø 50 mm	554090 50
Rubber backing pad shank Ø 6 mm soft External Ø 50 mm	554091 50