



## Abrasive flap disc V2 Power, (CER), flat-dished for stainless steel, 230 mm Ø, Grit: 40



### Order data

Order number	565484 40
GTIN	4027497481606
Item class	53L

### Description

#### Version:

**The patented sickle-shaped strip-form** and configuration permit a high coating density for an exceptional metal removal rate and a long tool life.

Glass fibre plate for **general-purpose use**.

Very high abrasion performance, **ceramic grit** with self-sharpening effect. No glazing or overheating. Highly suitable even for edge grinding.

#### Application:

Low-vibration working and long working life.

#### Note:

Padless flap discs SLTflex for gentle cutting, fillet weld smoothing etc. can be found under No. 566300 ff.

### Technical description

Disc Ø	230 mm
Grit	40

Bore Ø	22.23 mm
Shape description	flat-dished
Grinding medium code	Ceramic
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	230 mm Ø
Backing pad	Glass fibre pad
optimised for material	INOX
maximum circumferential speed	80 m/s
Type of product	Abrasive flap disc

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable only under restricted conditions		
dry	suitable		