



Cordless hammer drill / driver without battery or charger, Type: M18FPD2

Order data

Order number	070111 M18FPD2
GTIN	4002395810390
Item class	03L

Description

Version:

- **Powerful cordless 2-speed hammer drill /screwdriver with multi-stage torque setting.**
- **With overload protection for long working life of the battery, motor, and gearbox.**
- **REDLITHIUM-ION™ Red Li-ion batteries with single-cell monitoring and charge display.**
- **Sturdy metal gearbox for long working life.**
- **FIXTEC metal quick-change chuck with spindle lock.**
- **Handle with Softgrip coating for comfortable use.**
- **LED illumination of the working area.**
- **Brushless POWERSTATE™-motor (not size M18BPD4) for very high efficiency. Very low wear and up to 10 times the working life of standard DC motors.**
- **REDLINK PLUS™ electronics overload protection and power management.**

Low-maintenance, brushless Powerstate motor.

Feature:

Low-maintenance, brushless Powerstate motor.

Supplied with:

Zero version – without battery, charger or transport case, with belt clip.

Note:

See No. 073814ff and No. 073840 for suitable batteries and chargers. Suitable Bluetooth tracking modules can be found in the online shop under No. 070103 TICK.

Packaging: Modular case (HD=Heavy Duty)

suitable battery - supplier / battery type / voltage: Milwaukee type B 18 V

Motor design: Brushless

Battery voltage: 18 V

Battery capacity: 2 A·h

maximum speed 1st speed: 0 - 550 rpm

maximum speed 2nd speed: 2000 rpm

maximum torque: 125 N·m

Technical description

Type of product
